

INTRODUCING

NECTOR T SPLICE CONNECTOR

- Improves installation efficiency with easy-to-use screw termination
- Suited to broad range of wire sizes (1.5mm² to 4.0mm²)



TE Connectivity (TE)'s NECTOR T splice portfolio includes IP67/IP68 rated field installable connectors with standard M3 screw termination. NECTOR T splice connectors offer a new solution to high humidity and harsh environment installations like horticultural and outdoor lighting. It is an easy-to install and time saving alternative to traditional hard-wired electrical connections.

KEY BENEFITS

- Improves installation efficiency with easy-to-use screw termination
- Suited to broad range of wire sizes (1.5mm² to 4.0mm²)
- IP67/68 rated for moisture tight application
- Easy maintenance

APPLICATIONS

- Horticultural and greenhouse lighting
- Garden lighting
- Outdoor displays
- Parking and garage lighting
- Stadium lighting
- Outdoor electrical installations

LEARN MORE

- [NECTOR T Splice Product Flyer](#)
- [NECTOR T Splice CF Part Number List](#)
- [NECTOR T Splice Power Systems Horticultural Lighting](#)